

SETARI PENTRU APARATUL ARIAC PLUS

Apparatus Information

Manufacturer: Model:

Apparatus Type

- Compressed Air Breathing Apparatus
- Airline Apparatus
- Combination CABA/Airline
- Cylinder
- Hood
- Closed Circuit Breathing Apparatus
- Chemical Protection Suit

Supply Pressure

- 200 bar
- 300 bar

Apparatus Type | Apparatus Information | Leak, Alarm Test Parameters

Activation/Static Test | Breathing Test Parameters | Pressure Gauge Test

Apparatus Information

Manufacturer: Model:

First Breath Activation Pressure

- Yes
- No

Allow 40 x 2.5 L/min Work in Breathing Tests

- Yes
- No

Perform Medium Pressure Tests

- Yes
- No

Gauge Type

- Fraction/Percent
- Digital
- Numbers
- HUD with no other gauge

Alarm Type

- Bell
- Whistle
- LED

Redundant Low Pressure Alarm

- Yes
- No

High Pressure Hose Volume

Liters

Apparatus Type | **Apparatus Information** | Leak, Alarm Test Parameters

Activation/Static Test | Breathing Test Parameters | Pressure Gauge Test

SETARI PENTRU APARATUL ARIAC PLUS

Apparatus Information ✕

Manufacturer: Model:

High Pressure Leak Test

Test Duration: Sec.

Pressure Change Allowed: bar

Alarm Activation Pressure

Minimum: bar

Maximum: bar

Facepiece Leak Test

Starting Pressure: mbar

Allowable Leakage: mbar

Test Duration: Sec.

Exhalation Valve Opening Pressure

Minimum: mbar

Maximum: mbar

Apparatus Type

Apparatus Information

Leak, Alarm Test Parameters

Activation/Static Test

Breathing Test Parameters

Pressure Gauge Test

Apparatus Information ✕

Manufacturer: Model:

Static Facepiece Pressure

Delay:

Minimum: mbar

Maximum: mbar

Medium Pressure Change

Maximum: bar

Static Medium Pressure

Minimum: bar

Maximum: bar

Safety Valve Opening Pressure

Minimum: bar

Maximum: bar

Bypass Flow

Minimum: L/min

Maximum: L/min

Activation/Static Test

Breathing Test Parameters

Pressure Gauge Test

Apparatus Type

Apparatus Information

Leak, Alarm Test Parameters

SETARI PENTRU APARATUL ARIAC PLUS

Apparatus Information

Manufacturer: Model:

Breathing Resistance Facepiece Pressure

25 x 2 L/min Breathing Rate	40 x 2.5 L/min Breathing Rate
Minimum: <input type="text" value="0.1"/> mbar	Minimum: <input type="text" value="0.1"/> mbar
Maximum: <input type="text" value="7"/> mbar	Maximum: <input type="text" value="10"/> mbar

Dynamic Medium Pressure

25 x 2 L/min Breathing Rate	40 x 2.5 L/min Breathing Rate
Minimum: <input type="text" value="4.5"/> bar	Minimum: <input type="text" value="4"/> bar
Maximum: <input type="text" value="8.5"/> bar	Maximum: <input type="text" value="9.5"/> bar

Activation/Static Test **Breathing Test Parameters** Pressure Gauge Test

Apparatus Type Apparatus Information Leak, Alarm Test Parameters

Apparatus Information

Manufacturer: Model:

Pressure Gauge Test

Maximum Error: bar

Maximum Error at Test Point 3: bar

Pressure Gauge Test Points

Test Point 1 (Highest): bar

Test Point 2: bar

Test Point 3 (Lowest): bar

Activation/Static Test Breathing Test Parameters **Pressure Gauge Test**

Apparatus Type Apparatus Information Leak, Alarm Test Parameters

TASTA "OK" SE APASA DOAR DUPA CE S-AU INTRODUS SETARILE IN TOATE CELE 6 FERESTRE PENTRU CONFIRMARE.